

**clangsonic**

**clangsonic**

[www.clangsonicultrasonics.com](http://www.clangsonicultrasonics.com)

## **Ultrasonic Cleaner 40l**



RT Ultrasonic Cleaner 40l is suitable for lab use, jewelry, glasses, lenses and industrial superfine components cleaning. It is developed based on the advanced Full Bridge Phase Shift technology and equipped with LCD display, timer, heater and so on, easy to operate and no need to debug. It is widely used in metal parts, auto parts, electronics and medical industries etc.

## **Buy Customized Ultrasonic Cleaner 40l From China**

### **1.Ultrasonic Cleaner 40l Introduction**

RT ultrasonic cleaner is suitable for lab use, jewelry, glasses, lenses and industrial superfine components cleaning. It is developed based on the advanced Full Bridge Phase Shift technology and equipped with LCD display, timer, heater and so on, easy to operate and no need to debug. It is widely used in metal parts, auto parts, electronics and medical industries etc.



## Four reasons why our product shall be your best choice:

1. Large LCD display screen
2. High strength aluminum alloy handle
3. High Grade SUS Anodized inner Tank
4. Transducer, ultrasonic generator and metal sheet all made in-house to ensure optimum matching



Clangsonic provides varies of capacities of ultrasonic cleaner. Please contact us for customized tank size.

## 2. Ultrasonic Cleaner 40l Parameter (Specification)

Name	Laboratory Ultrasonic Cleaner
Model	R40
Capacity	40L
Transducer QTY	18PCS
Ultrasonic Frequency	28/kHz or 40kHz
Ultrasonic Power	900W
Heating Power	400W
Heating Temperature	0-60°C
Timing	0-99min. or Normally Open
Inner Tank Size	Customized
Basket Size	Customized
Overall Size	Customized
Power Supply	220V±10V, 50Hz (Please remark it when placing order)
SUS Basket	√
N.W	18KGS
G.W	24KGS

## 3. Ultrasonic Cleaner 40l Features and Application

1. Thermostatically adjustable: 0~60°C.
2. Auto save setting parameters
3. Timer for countdown and continuous operation
4. Sweep for permanent sound field oscillation
5. Freely reset to default settings
6. Pulse-degassing can greatly remove unnecessary air bubble and have better cleaning effect



#### 4.Ultrasonic Cleaner 40l Details Images



Panel

LCD display

High definition and resolution ratio, abundant display contents(operational menu)with less power consumption and functions of timing, heating and degassing.



Material

Excellent imported checked SUS

Slap-up and robust checked SUS, attractive and durable.



Handle

Aluminum Alloy Handle

Industrial level, longer lifespan and high strength  
which can bear heavy duty workpieces



Tank

SUS Tank

Made in imported SUS 304 with special  
surface treatment to expand the service time  
and resistance to corrosion from  
ultrasonic cavitation



Valve

Ball Valve

One-piece welding process 1/2" valve,  
excellent waterproof and durability



**5.Ultrasonic Cleaner 40l Company Qualification**



## clangsonic

Yuhuan Clangsonic Ultrasonic Co., Ltd. is a professional engaged in ultrasonic transducer, ultrasonic shock box, ultrasonic (generator) power and ultrasonic equipment research and application of the manufacturer.

Since 2003 the company since its establishment, unswervingly adhere to the higher quality and better service as our ultimate goal.

Our products are exported to the world more than 40 countries and regions. To provide customers with a full range of ultrasonic products and solutions, so that waves of the company to become a global customer real partners.



The company has an effective construction area of over 6,000 square meters, with imported Tian Tian, Baichao sheet metal bending machine, KUKA robot, as well as the Swedish fuse factory, and CNC sawing machine, CNC lathe, CNC milling machine and other equipment, making the product more reliable.


### Visit Factory



### Workshop



### Exhibition









01  
Wrapped in dustproof film bag



02  
Shockproof EPS boards



03  
Outer box for double-protection



04  
Sealed with multilayer adhesive tape



05  
Plastic-belt for reinforcement



06  
Ready to ship

CLANGSONIC

## Shipping & Payment

Started working again,Started working again,Started working again.



### 7. FAQ

#### 1. Are you manufacturer or trading company?

We are manufacturer. All the core components (ultrasonic transducer, ultrasonic generator) are home-made by ourselves.

#### 2. Do you accept OEM and ODM?

Yes, we also have profession R&D teams (ultrasonic transducer team, ultrasonic generator team and mechanical design team) to responds your special needs quickly.

#### 3. Delivery time

Standard products can be delivered within 7 working days. Customized machine depend on the design.

**4. Warranty**

We guarantee quality of the products for a period of 1 year. If any quality problem within warranty, we'll provide free spare parts or repairing service.

**5. Do you provide trial cleaning service?**

Yes, you're welcome to send the workpieces for trial cleaning. We'll send you video and report about the test. It's free service.

**6. Can you provide ultrasonic transducer or generator if any failure?**

Yes, ultrasonic transducer and ultrasonic generator are designed and manufactured by ourselves. We can send the right parts quickly for replacement.

**7. Payment Methods?**

T/T ,L/C, D/P ,D/A, West Union , Paypal, MoneyGram ,Escrow .

**8. Which frequency and power is suitable for our workpiece?**

Please contact us and provide details as specific as you can. Information includes: the size, material, weight and dirt of your workpiece and cleaning tank dimension etc.